



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F40C50ECO 40W T12 48" 5000K 90 Cri Bi-Pin Fluorescent

Ge By Current Lamps

Catalog Number	F40C50ECO
Manufacturer	Ge By Current Lamps
Description	Ge Ecolux®, 40 WTT, 2250 LM, 5000 KV, 90 Cri, 1.5 In Diameter, 48 In Length, Medium Bi-Pin (G13) Base, 20000 HR Average Life
Weight per unit	0.4100 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

average life	20000.0
Base	Medium Bi-Pin (G13)
lumens	2250.0
Wattage	40.0

Material, Color, and Finish

color rendering index (cri)	90.0
color temperature	5000.0

Dimensions and Weight

Diameter	1.5
Length	48.0

Descriptions

Description	40W T12 48" 5000K 90 CRI BI-PIN FLUORESCENT
extra long description	GEL F40C50/ECO 80096 FLUORESCENT F4
Long Description	GE Ecolux®, 40 WTT, 2250 LM, 5000 KV, 90 CRI, 1.5 IN Diameter, 48 IN Length, Medium Bi-Pin (G13) Base, 20000 HR Average Life
Product Type	80096 Fluorescent F40

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168800969
Manufacturers Part Number	F40C50/ECO
UPC	043168800969

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Packaging

Carton	1
Package	30
Weight Per each	0.41

Uses, Certifications, and Standards

Application	Full Wattage
-------------	--------------