



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F40DX 40W T12 48" 6500K 88CRI By-Bin Daylight Rapid Star

Sylvania-Ledvance

Catalog Number	F40DX
Manufacturer	Sylvania-Ledvance
Description	40W, T12 Rapid Start Fluorescent Lamp, Daylight Deluxe Phosphor, 6500K Color Temperature, 88 Cri. 20000 Avg Rated Life At 3 HRS/Start, 28800 Avg Rated Life At 12 HRS/Start. Vivid Color: High Cri Lamps For Color Critical Applications
Weight per unit	0.6670 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Medium Bipin
beam angle	Universal
bulb type	T12
Lamp Type	RAPID START
lumens	2180 Initial Lumens at 25 Degrees C
Shape	T12
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	40

Material, Color, and Finish

color rendering index (cri)	88
color temperature	6500

Descriptions

Description	40W T12 48" 6500K 88CRI BY-BIN DAYLIGHT RAPID STAR
extra long description	SYL F40DX/24477 F40DX 30/CS 1/SKU
Long Description	40W, T12 rapid start fluorescent lamp, Daylight Deluxe phosphor, 6500K color temperature, 88 CRI. 20000 Avg rated life at 3 hrs/start, 28800 Avg rated life at 12 hrs/start. VIVID Color: High CRI lamps for color critical applications

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135244773
Manufacturers Part Number	F40/DX/24477
UPC	046135244773

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 30

Weight Per each 0.667

Uses, Certifications, and Standards

Application Commercial/Residential

standard ANSI C78.81 - 2001