



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## F54T5850EC0H0CVG 54W T5 46" SHTR Res 50K Min Bipin

*Ge By Current Lamps*

Catalog Number	F54T5850EC0H0CVG
Manufacturer	Ge By Current Lamps
Description	Shatter Resistant Fluorescent Lamp, T5 Shape, 85, 5000 K, 4370 LM Brightness (Lumens), 54 W, 520 V, 460 Ma, 30000 H Average Life, G5 Miniature Bi-Pin Base, Non Dimmable, 0.62 In Diameter, 45.2 In Length, Rapid, 0.4 LB
Weight per unit	0.4000 (lbs/each)
Product Category	Shatter Resistant Fluorescent

### Features

Base	Miniature Bi-Pin (G5)
lumens	4650.0
Wattage	54.0

### Material, Color, and Finish

color rendering index (cri)	85.0
-----------------------------	------

### Dimensions and Weight

Length	45.2
--------	------

### Descriptions

Description	54W T5 46" SHTR RES 50K MIN BIPIN
extra long description	GEL F54T5850HOECOCVG 80311 FLUORESC

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168803113
UPC	043168803113

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

### Packaging

Carton	1
Package	40
Weight Per each	0.4

### Uses, Certifications, and Standards

Application	Shatter-Resistant
-------------	-------------------