



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F54T5850EC0H0CVG 54W T5 46" SHTR Res 50K Min Bipin

Ge By Current Lamps

Catalog Number	F54T5850EC0H0CVG
Manufacturer	Ge By Current Lamps
Description	Shatter Resistant Fluorescent Lamp, T5 Shape, 85, 5000 K, 4370 LM Brightness (Lumens), 54 W, 520 V, 460 Ma, 30000 H Average Life, G5 Miniature Bi-Pin Base, Non Dimmable, 0.62 In Diameter, 45.2 In Length, Rapid, 0.4 LB
Weight per unit	0.4000 (lbs/each)
Product Category	Shatter Resistant Fluorescent

Features

Base	Miniature Bi-Pin (G5)
lumens	4650.0
Wattage	54.0

Material, Color, and Finish

color rendering index (cri)	85.0
-----------------------------	------

Dimensions and Weight

Length	45.2
--------	------

Descriptions

Description	54W T5 46" SHTR RES 50K MIN BIPIN
extra long description	GEL F54T5850HOECOCVG 80311 FLUORESC

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168803113
UPC	043168803113

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Packaging

Carton	1
Package	40
Weight Per each	0.4

Uses, Certifications, and Standards

Application	Shatter-Resistant
-------------	-------------------