



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## **F60T12DH0 75W T12 60" Daylight High Output 76 Cri R17D**

*Ge By Current Lamps*

Catalog Number	F60T12DH0
Manufacturer	Ge By Current Lamps
Description	Fluorescent Lamp, Recessed Double Contact R17D Base, T12 Bulb Shape, 75, 12000 H Average Life, 6500 K, 75 W, 4400 LM Brightness (Lumens), Soda Lime Housing Material, 1.5 In Diameter, 60.0 In Length, Rapid, -29 °C Operating Temperature, 0.87 LB/Ea
Weight per unit	0.8400 (lbs/each)
Product Category	Linear Fluorescent Straight La

### **Features**

Base	Recessed Double Contact (R17d)
lumens	4400.0
Wattage	75.0

### **Material, Color, and Finish**

color rendering index (cri)	75.0
-----------------------------	------

### **Dimensions and Weight**

Diameter	1.5
----------	-----

### **Descriptions**

Description	75W T12 60" DAYLIGHT HIGH OUTPUT 76 CRI R17D
extra long description	GEL F60T12/D/HO-15PK 23077 FLUORE

### **Manufacturer Information**

Brand	GE Current, a Daintree company
GTIN	00043168230773
Manufacturers Part Number	F60T12/D/HO 15PK
UPC	043168230773

### **Taxonomies, Classifications, and Categories**

Category Description	Fluorescent
----------------------	-------------

### **Packaging**

Carton	1
Package	15
Weight Per each	0.84