



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## F60T12DHO \*Delisted\* 75W T12 60" Daylight Ho 76 Cri R17D

*Sylvania-Ledvance*

Catalog Number	F60T12DHO
Manufacturer	Sylvania-Ledvance
Description	OBS25120 75W, 60"Mol, T12 Ho (800 Ma) Rapid Start Fluorescent Lamp, Daylightphosphor, 6500K Color Temperature, 72 Cri
Weight per unit	0.8600 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

amperage rating	Ballast Dependent
average life	12000
Base	Recessed Double Contact
bulb type	T12
lumens	4600 Initial Lumens at 25 Degrees C
Shape	T12
start type	Rapid Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	75

### Material, Color, and Finish

color rendering index (cri)	76
color temperature	6500
Finish	Phosphor Coated

### Dimensions and Weight

Diameter	1.5 in
----------	--------

### Descriptions

Description	*DELISTED* 75W T12 60" DAYLIGHT HO 76 CRI R17D
extra long description	SYL F60T12/D/HO/25120 F60T12DHO 30/
Long Description	OBS25120 75W, 60"MOL, T12 HO (800 mA) rapid start fluorescent lamp, Daylightphosphor, 6500K color temperature, 72 CRI
Product Type	F60T12DHO 30/CS 1/Sku

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135251207
Manufacturers Part Number	F60T12/D/HO/25120
UPC	046135251207



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description Fluorescent

Type FLUORESCENT

## Packaging

Carton 1

Package 30

Weight Per each 0.86

## Uses, Certifications, and Standards

Application Commercial/Residential