



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F72T8CW 38W 200MA Fluor Lamp

Sylvania-Ledvance

Catalog Number	F72T8CW
Manufacturer	Sylvania-Ledvance
Description	38W, 72" Mol, T8 Instant Start Slimline Fluorescent Lamp, Cool White Phosphor, 4200K Color Temperature, 60 Cri
Weight per unit	0.6667 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
average life	7500
Base	Single Pin
bulb type	T8
lumens	3050 Initial Lumens at 25 Degrees C
Shape	T8
start type	Instant Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	38

Material, Color, and Finish

color rendering index (cri)	60
color temperature	4200
Finish	Phosphor Coated

Dimensions and Weight

Diameter	1
----------	---

Descriptions

Description	38W 200MA FLUOR LAMP
extra long description	SYL F72T8CW/27266 F72T8CW 24/CS 1/S
Long Description	38W, 72" MOL, T8 instant start Slimline fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI
Product Type	F72T8CW 24/CS 1/Sku
Special Features	COOL WHITE

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135272660
Manufacturers Part Number	F72T8/CW/27266
UPC	046135272660



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	24
Weight Per each	0.6667

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------