



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F88G24 8X8X24 N1 HC STRT SCT

Hoffman Enclosures, Inc.

Catalog Number	F88G24
Manufacturer	Hoffman Enclosures, Inc.
Description	Lay-In Wireway, Gray, Polyester Powder Paint, Steel, Hinged Cover, 8 In Overall Height, 24 In Overall Length, 8 In Overall Width, 18.5 LB
Weight per unit	18.5 (lbs/each)
Product Category	Nema Type 1 Wireway & Fittings

Features

ip rating	IP30
Knockouts	NO

Material, Color, and Finish

Color Code	ANSI 61
Style	Liftoff Cover no Knockouts

Dimensions and Weight

Height	8
Width	8

Descriptions

Description	8X8X24 N1 HC STRT SCT
extra long description	NVENT HOF F88G24 24.00in Straight S
Features	Lay-in Hinged-Cover Type 1 Straight Sections are used for enclosing wire and cable in wireway runs. Sections are completely open on one side so wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system. Sections are available in lengths from 12 inch to 120 inch, with or without knockouts.

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510526108
UPC	783510526108

Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	Straight Section

Packaging

Carton	1
Weight Per each	18.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

nema rating

Power Distribution

1 Indoor, electrical protection