



GE
Lighting

66862 - F96T12HL41/HO/WM

F96T12HL41/HO/WM-CIRCLEVILLE C AND I SKUS IN PULP



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight
	Linear
Bulb	T12
Base	Recessed Double -Contact (R17d)
Rated Life	12000.0 hrs
Bulb Material	Sodalime glass
LEED-EB MR Credit	947 picograms Hg per mean lumen hour
Primary Application	Energy Saving

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	8850.0
Mean Lumens	7920.0
Nominal Initial Lumens per Watt	93
Color Temperature	4100.0 K
Color Rendering Index (CRI)	77.0

ELECTRICAL CHARACTERISTICS

Wattage	95.0
---------	------

DIMENSIONS

Maximum Overall Length (MOL)	96.0000 in(2438.4 mm)
Nominal Length	96.000 in(2438.4 mm)
Bulb Diameter (DIA)	1.500 in(38.1 mm)

PRODUCT INFORMATION

Product Code	66862
Description	F96T12HL41/HO/WM
Standard Package	Case
Standard Package GTIN	10043168668627
Standard Package Quantity	15
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	15
UPC	043168668620