




GE
Lighting

68871 - F96T8/XL/SPX50/2
F96T8/XL/SPX50/2



GENERAL CHARACTERISTICS

| | |
|----------------------------|-------------------------------|
| Lamp Type | Linear Fluorescent - Straight |
| | Linear |
| Bulb | T8 |
| Base | Single Pin (Fa8) |
| Rated Life (NOM) | 24000.0 h |
| Bulb Material | Sodalime glass |
| Starting Temperature (MIN) | 10.0 °C |
| Mercury Content (NOM) | 90.0 mg |
| Picograms of Mercury (NOM) | 663.7168 pg |
| Primary Application | Full Wattage |

PHOTOMETRIC CHARACTERISTICS

| | |
|---------------------------------------|----------|
| Initial Lumens (NOM) | 5950.0 |
| Mean Lumens (NOM) | 5650.0 |
| Nominal Initial Lumens per Watt (NOM) | 100.8475 |
| Color Temperature (NOM) | 5000.0 K |
| Color Rendering Index (CRI) (NOM) | 82.0 |

ELECTRICAL CHARACTERISTICS

| | |
|---------------|------|
| Wattage (NOM) | 59.0 |
|---------------|------|

DIMENSIONS

| | |
|------------------------------------|----------------------|
| Maximum Overall Length (MOL) (NOM) | 96.000 in(2438.4 mm) |
| Nominal Length (NOM) | 96.000 in(2438.4 mm) |
| Bulb Diameter (DIA) (NOM) | 1.000 in(25.4 mm) |


PRODUCT INFORMATION

| | |
|----------------------------------|------------------|
| Product Code | 68871 |
| Description | F96T8/XL/SPX50/2 |
| Standard Package | Case |
| Standard Package GTIN | 10043168688717 |
| Standard Package Quantity | 24 |
| Sales Unit | Unit |
| No Of Items Per Sales Unit | 1 |
| No Of Items Per Standard Package | 24 |
| UPC | 043168688710 |



GE
Lighting

68871 - F96T8/XL/SPX50/2
F96T8/XL/SPX50/2



GENERAL CHARACTERISTICS

| | |
|----------------------------|-------------------------------|
| Lamp Type | Linear Fluorescent - Straight |
| | Linear |
| Bulb | T8 |
| Base | Single Pin (Fa8) |
| Rated Life (NOM) | 24000.0 h |
| Bulb Material | Sodalime glass |
| Starting Temperature (MIN) | 10.0 °C |
| Mercury Content (NOM) | 90.0 mg |
| Picograms of Mercury (NOM) | 663.7168 pg |
| Primary Application | Full Wattage |

PHOTOMETRIC CHARACTERISTICS

| | |
|---------------------------------------|----------|
| Initial Lumens (NOM) | 5950.0 |
| Mean Lumens (NOM) | 5650.0 |
| Nominal Initial Lumens per Watt (NOM) | 100.8475 |
| Color Temperature (NOM) | 5000.0 K |
| Color Rendering Index (CRI) (NOM) | 82.0 |

ELECTRICAL CHARACTERISTICS

| | |
|---------------|------|
| Wattage (NOM) | 59.0 |
|---------------|------|

DIMENSIONS

| | |
|------------------------------------|----------------------|
| Maximum Overall Length (MOL) (NOM) | 96.000 in(2438.4 mm) |
| Nominal Length (NOM) | 96.000 in(2438.4 mm) |
| Bulb Diameter (DIA) (NOM) | 1.000 in(25.4 mm) |

PRODUCT INFORMATION

| | |
|----------------------------------|------------------|
| Product Code | 68871 |
| Description | F96T8/XL/SPX50/2 |
| Standard Package | Case |
| Standard Package GTIN | 10043168688717 |
| Standard Package Quantity | 24 |
| Sales Unit | Unit |
| No Of Items Per Sales Unit | 1 |
| No Of Items Per Standard Package | 24 |
| UPC | 043168688710 |