



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FEML484LMVOLT 4' Led VPR PRF 40K 4000LM

Lithonia Lighting - Acuity

Catalog Number	FEML484LMVOLT
Manufacturer	Lithonia Lighting - Acuity
Description	Low-Profile Enclosed and Gasketed Industrial Led , 48" Long, Four Lamps, 120V-277V
Weight per unit	13.7 (lbs/each)
Product Category	Lighting

Features

average life	60,000
connection	Hardwired
Fixture Type	Linear
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Static
lumens	4,000
Number of Lamps	4
pallet quantity	30
Shape	Rectangular
Voltage Rating	120 to 277
Warranty	1

Material, Color, and Finish

Color	White
Lens Color	Clear
Style	Traditional

Dimensions and Weight

Height	4.2
Length	51.75
Size	51.75x6.8x4.2 IN
Width	6.8

Descriptions

Description	4' LED VPR PRF 40K 4000LM
extra long description	LITH FEM L48 4L MVOLT Linear
Long Description	Low-profile enclosed and gasketed industrial LED , 48" long, Four lamps, 120V-277V
Product Type	Linear



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00194994110323
Manufacturers Part Number	FEM L48 4L MVOLT
UPC	194994110323

Taxonomies, Classifications, and Categories

Category Description	LED HAZARDOUS LOCATION & VAPOR TIGHT LIGHTING
Type	LINEAR

Trade Size

aperture size	4FT
---------------	-----

Packaging

Carton	1
Weight	11.2
Weight Per each	13.7

Uses, Certifications, and Standards

Application	Automotive & Parking, Enclosed & Gasketed, Government, Manufacturing, Parking Garage, Special Applications, Sports and Recreation, Warehouses
environmental conditions	Demanding, Indoor
Mounting	Pendant, Surface, Suspended
standard	CSADLC Premium, DLC Standard