

Eaton FH42

Catalog Number: FH42

Eaton A200/B100 heater, Used with Starter Sizes 0,1, and 2, A200/B100 Heater, NEMA, Ambient 10.4-11.3, 12.0-13.1A, Non-Comp 9.6-10.5, 11.8-12.7A, Used with Starter Sizes 0,1, and 2, Type A and B, Thermal and Fast Trip



General specifications

Product Name

Eaton A200/B100 heater

UPC

786678670126

Product Height

0.8 in

Product Weight

0.04 lb

Certifications

UL Listed
CSA Certified

Catalog Number

FH42

Product Length/Depth

2.1 in

Product Width

1.4 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Catalog Notes

Select heater coils based on full load current (FLA) shown on motor nameplate. Heater coils are rated to protect 40 degree C rise and a service factor of 1.15, Single-Phase requires 2 heaters, Three-Phase Requires 3 heaters.

[Special features](#)

Used with Starter Sizes 0,1, and 2

[Type](#)

A200/B100 Heater

[Used with](#)

Used with Starter Sizes 0,1, and 2

[Design](#)

NEMA

[Full load current range](#)

Ambient 10.4-11.3, 12.0-13.1 A, Non-Comp 9.6-10.5, 11.8-12.7
A

[Overload relay](#)

Type A and B

[Trip type](#)

Thermal and fast trip

[Catalogs](#)

[Eaton's Volume 5—Motor Control and Protection](#)

[Installation instructions](#)

[Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers](#)

[Specifications and datasheets](#)

[Eaton Specification Sheet - FH42](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)