




GE
Lighting

89632 - FLE15/2/A19XL

GE A19

 High Color Rendering
cUL Listed
Energy Savings



GENERAL CHARACTERISTICS

Lamp Type	Compact Fluorescent - Self-Ballasted
Bulb	A19
Base	Medium Screw (E26)
Bulb Finish	Soft white
Equivalent Wattage (NOM)	60.0 W
Rated Life (NOM)	10000.0 h
Starting Temperature (MIN)	5.0 °C
Total Harmonic Distortion (THD) (NOM)	120.0 %
Mercury Content (NOM)	3.5 mg
Picograms of Mercury (NOM)	530.3 pg
Primary Application	Standard

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	825.0
Mean Lumens (NOM)	660.0
Nominal Initial Lumens per Watt (NOM)	55.0
Color Temperature (NOM)	2700.0 K
Color Rendering Index (CRI) (NOM)	82.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	15.0
Voltage (NOM)	120.0
Input Voltage (NOM)	120.0 V
Input Current (NOM)	0.17 A
Power Factor (NOM)	0.6

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	4.600 in(116.8 mm)
Nominal Length (NOM)	4.600 in(116.8 mm)
Bulb Diameter (DIA) (NOM)	2.375 in(60.3 mm)

PRODUCT INFORMATION

Product Code	89632
Description	FLE15/2/A19XL
Standard Package Case	Case
Standard Package GTIN	10043168896327
Standard Package Quantity	10
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
Package UPC	043168896320




GE
Lighting

89632 - FLE15/2/A19XL

GE A19

 High Color Rendering
cUL Listed
Energy Savings



GENERAL CHARACTERISTICS

Lamp Type	Compact Fluorescent - Self-Ballasted
Bulb	A19
Base	Medium Screw (E26)
Bulb Finish	Soft white
Equivalent Wattage (NOM)	60.0 W
Rated Life (NOM)	10000.0 h
Starting Temperature (MIN)	5.0 °C
Total Harmonic Distortion (THD) (NOM)	120.0 %
Mercury Content (NOM)	3.5 mg
Picograms of Mercury (NOM)	530.3 pg
Primary Application	Standard

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	825.0
Mean Lumens (NOM)	660.0
Nominal Initial Lumens per Watt (NOM)	55.0
Color Temperature (NOM)	2700.0 K
Color Rendering Index (CRI) (NOM)	82.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	15.0
Voltage (NOM)	120.0
Input Voltage (NOM)	120.0 V
Input Current (NOM)	0.17 A
Power Factor (NOM)	0.6

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	4.600 in(116.8 mm)
Nominal Length (NOM)	4.600 in(116.8 mm)
Bulb Diameter (DIA) (NOM)	2.375 in(60.3 mm)

PRODUCT INFORMATION

Product Code	89632
Description	FLE15/2/A19XL
Standard Package Case	Case
Standard Package GTIN	10043168896327
Standard Package Quantity	10
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
Package UPC	043168896320