



FNM3 3A 250V TD Midget Fuse

Bussmann Fuses

Catalog Number	FNM3
Manufacturer	Bussmann Fuses
Description	Fuse, Time Delay Fuse Speed, Class CC Fuse, Ferrule End X Ferrule End Connection, 3 A, 250 V Ac, Melamine (Tube);Brass (Cap) Material, Dual Element, 0.41 In Diameter, 1.5 In Overall Length, 0.125 LB
Weight per unit	0.0100 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	3 Amp
class	Supplemental
connection	Ferrule End X Ferrule End
dimensions	0.3900 IN X 0.3900 IN X 1.4400 IN
element	Dual
media	Yes

Dimensions and Weight

Size	13/32 In Diameter X 1-1/2 In Length
------	-------------------------------------

Descriptions

Description	3A 250V TD MIDGET FUSE
extra long description	BUSS FNM-3 BUSS MIDGET FUSE
Special Features	Nickle Plated Brass Endcap

Manufacturer Information

Brand	Eaton Bussmann series
GTIN	00051712520300
UPC	051712520300

Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	FUSE

Packaging

Carton	10
Weight Per each	0.01

Uses, Certifications, and Standards

standard	RoHS Compliant,CE Marked
----------	--------------------------