



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FNQR118 1-1/8A 600V TD Class CC Fuse

Bussmann Fuses

Catalog Number	FNQR118
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series Class CC Fuse, FNO, Time-Delay, Dual-Element Current Limiting Fuse, 1.125 A, Rejection Style Fuse, Interrupting Rating Of 200KA At 600vac
Weight per unit	0.0200 (lbs/each)
Product Category	Small Dimension Fuses

Features

media	Yes
-------	-----

Descriptions

Description	1-1/8A 600V TD CLASS CC FUSE
extra long description	BUSS FNQ-R-1-1/8 CLASS CC TIME DELA
Features	Bussmann's Class CC fuses set the standard in Class CC fuse performance in the industry. Recognized for their superior performance, Bussmann has the right product for your circuit and equipment protection needs. These branch circuit rated, 600v, 200,000a IR fuses offer exceptional protection in the smallest package of any UL class of fuses. Choose from the ultimate protection provided by our Low Peak LP-CC fuses, the time delay of our FNQ-R's for your control transformer and similar control applications or
Long Description	Eaton Bussmann Series Class CC fuse, FNQ, time-delay, dual-element current limiting fuse, 1.125 A, rejection style fuse, interrupting rating of 200kA at 600Vac
Product Type	Class CC Time Delay

Manufacturer Information

Brand	Eaton
GTIN	00051712497053
Manufacturers Part Number	FNQ-R-1-1/8
UPC	051712497053

Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
----------------------	--------------

Packaging

Carton	10
Weight Per each	0.02