



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FNQR30 30A 600V TD Class CC Fuse

Bussmann Fuses

Catalog Number	FNQR30
Manufacturer	Bussmann Fuses
Description	Fuse, Time Delay Fuse Speed, Class CC Fuse, 12 S @ 200% Response Time, Ferrule End X Ferrule End Connection, 30 A, 600 V Ac, Melamine Material, 0.41 In Diameter, 1.5 In Overall Length, 0.02 LB
Weight per unit	0.0200 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	30
class	Class CC
connection	Ferrule End X Ferrule End
dimensions	1.5000 IN X 0.4100 IN X 0.4100 IN

Dimensions and Weight

Size	13/32 In Diameter X 1-1/2 In Length
------	-------------------------------------

Descriptions

Description	30A 600V TD CLASS CC FUSE
extra long description	BUSS FNQ-R-30 CLASS CC TIME DELAY
Features	Bussmann's Class CC fuses set the standard in Class CC fuse performance in the industry. Recognized for their superior performance, Bussmann has the right product for your circuit and equipment protection needs. These branch circuit rated, 600v, 200,000a IR fuses offer exceptional protection in the smallest package of any UL class of fuses. Choose from the ultimate protection provided by our Low Peak LP-CC fuses, the time delay of our FNQ-R's for your control transformer and similar control applications or
Special Features	Rejection Style

Manufacturer Information

Brand	Eaton
GTIN	00051712497145
UPC	051712497145

Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	FUSE

Packaging

Carton	10
Weight Per each	0.02



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

RoHS Compliant, CE Marked
