



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FP39841HOECO 39W T5 41K 85cri

Sylvania-Ledvance

Catalog Number	FP39841HOECO
Manufacturer	Sylvania-Ledvance
Description	39W, T5 Pentron High Output (Ho) Fluorescent Lamp, 4100K Color Temperature, Rare Earth Phosphor, 85 Cri, Ecologic
Weight per unit	0.1900 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
average life	25000
Base	Miniature Bipin
bulb type	T5
Lamp Type	PROGRAMMED RAPID START
lumens	3,100
Shape	T5
start type	Programmed Rapid Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	39

Material, Color, and Finish

color rendering index (cri)	85
color temperature	4100
Finish	Phosphor Coated

Dimensions and Weight

Diameter	0.625
----------	-------

Descriptions

Description	39W T5 41K 85CRI
extra long description	SYL FP39/841/HO/ECO/20934 FP39841HO
Long Description	39W, T5 PENTRON high output (HO) fluorescent lamp, 4100K color temperature, rare earth phosphor, 85 CRI, ECOLOGIC
Product Type	FP39841HOECO 40/CS 1/Sku
Special Features	COOL WHITE

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135209345
Manufacturers Part Number	FP39/841/HO/ECO/20934
UPC	046135209345



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	40
Weight Per each	0.19

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------