




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FP54835H0ECO T5 48" Mini Bipin High Output Fluorescent Lamp

Sylvania-Ledvance

Catalog Number	FP54835H0ECO
Manufacturer	Sylvania-Ledvance
Description	54W, T5 Pentron High Output (Ho) Fluorescent Lamp, 3500K Color Temperature, Rare Earth Phosphor, 85 Cri, Ecologic
Weight per unit	0.2700 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
average life	30000
Base	Miniature Bipin
bulb type	T5
Lamp Type	PROGRAMMED RAPID START
lumens	4450 Initial Lumens at 25 Degrees C
Shape	T5
start type	Programmed Rapid Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	54

Material, Color, and Finish

color rendering index (cri)	85
color temperature	3500
Finish	Phosphor Coated

Dimensions and Weight

Diameter	0.625
----------	-------

Descriptions

Description	T5 48" MINI BIPIN HIGH OUTPUT FLUORESCENT LAMP
extra long description	SYL FP54/835/HO/ECO/20904 FP54835HO
Long Description	54W, T5 PENTRON high output (HO) fluorescent lamp, 3500K color temperature, rare earth phosphor, 85 CRI, ECOLOGIC
Product Type	FP54835HOECO 40/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135209048
Manufacturers Part Number	FP54/835/HO/ECO/20904
UPC	046135209048



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description Fluorescent

Type FLUORESCENT

Packaging

Carton 1

Package 40

Weight Per each 0.27

Uses, Certifications, and Standards

Application Commercial/Residential