



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## FS1406HD 6' Fiberglass Stepladder

*Louisville Ladder*

|                  |  |
|------------------|--|
| Catalog Number   | FS1406HD   |
| Manufacturer     | Louisville Ladder  |
| Description      | Louisville; Step Ladder; Brute; Type Iaa; Ladder Height: 6 FT; Rung Size: 3 In; Base Size: 22-9/16 In Bottom Width; Material: Fiberglass; Load Capacity: 375 LB; Series: FS1400HD; Actual Cubic FT: 6.100 Cu-FT; Approx. Spread: 40-6/8 In |
| Weight per unit  | 21.0 (lbs/each)  |
| Product Category | Hand Tools - Ladders   |

### Features

|               |            |
|---------------|------------|
| Load Capacity | 375 W      |
| Material      | Fiberglass |

### Descriptions

|                  |  |
|------------------|--|
| Description      | 6' FIBERGLASS STEPLADDER   |
| Long Description | Louisville; Step Ladder; BRUTE; Type IAA; Ladder Height: 6 FT; Rung Size: 3 IN; Base Size: 22-9/16 IN Bottom Width; Material: Fiberglass; Load Capacity: 375 LB; Series: FS1400HD; Actual Cubic Ft: 6.100 CU-FT; Approx. Spread: 40-6/8 IN |
| Product Type     | Step Ladder, Louisville, Brute, Type Iaa, Csa, Ansi A14.5, Osha, 6...  |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Louisville     |
| GTIN                      | 00728865085801 |
| Manufacturers Part Number | FS1406HD       |
| sub brand                 | BRUTE          |
| UPC                       | 728865085801   |

### Taxonomies, Classifications, and Categories

|                      |          |
|----------------------|----------|
| Category Description | LADDERS  |
| Type                 | Type IAA |

### Packaging

|                 |    |
|-----------------|----|
| Carton          | 1  |
| Weight Per each | 21 |

### Uses, Certifications, and Standards

|          |                       |
|----------|-----------------------|
| standard | CSA, ANSI A14.5, OSHA |
|----------|-----------------------|