



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## FSD756D 20AWG Insld Pin TRML Panduit Corporation

|                  |  |
|------------------|--|
| Catalog Number   | FSD756D  |
| Manufacturer     | Panduit Corporation  |
| Description      | Polypropylene Insulated Ferrules Single Wire Whitedin End Sleeve, 20 Awg (.50MM <sup>2</sup> ), .24(6.0MM) Pin Length. |
| Weight per unit  | 0.1000 (lbs/each)  |
| Product Category | Small Terminals & Connectors   |

### Features

|            |               |
|------------|---------------|
| insulation | Polypropylene |
| Material   | Copper        |
| Wire Size  | 20            |

### Material, Color, and Finish

|        |        |
|--------|--------|
| Color  | White  |
| Finish | Tinned |

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 20AWG INSLTD PIN TRML  |
| extra long description | PAN FSD75-6-D Pan-Term® FSD75-6-D S  |
| Long Description       | Polypropylene insulated ferrules single wire whiteDIN end sleeve, 20 AWG (.50mm <sup>2</sup> ), .24(6.0mm) pin length. |
| Product Type           | Pan-Term® FSD75-6-D Single Wire Ferrules, Polypropylene, 20-   |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | PANDUIT        |
| GTIN                      | 00074983762446 |
| Manufacturers Part Number | FSD75-6-D      |
| UPC                       | 074983762446   |

### Taxonomies, Classifications, and Categories

|                      |                             |
|----------------------|-----------------------------|
| Category Description | TERMINALS                   |
| Type                 | Covered Single Wire Ferrule |

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Package         | 500 |
| Weight Per each | 0.1 |

### Uses, Certifications, and Standards

|                    |  |
|--------------------|--|
| Mounting standard  | 0.37<br>DIN 46228, CSA C22.2 No. 291-14, UL 486F, cULus 486F (with 20 AWG wire only) |
| Temperature Rating | 221 Degrees Fahrenheit (105 Degrees Celsius)   |