

GROUND CLAMPS
**Heavy Duty Direct Burial/
with Adapters & Rebar
Ground Clamps**
G-S DBR, G-BS, J-SB & RC SERIES



HEAVY DUTY BRONZE GROUND CLAMP



- Bronze ground clamp for bonding bare copper wire to copper water pipe.
- Assembled with tough 304 stainless steel screws.
- Available with silicon bronze screws by adding suffix -SB.
- cULus Listed 467 Grounding and Bonding.

All dimensional data is listed in inches.

CAT. NO.	GROUND WIRE RANGE	PIPE SIZE (IPS)	REBAR SIZE	GROUND ROD SIZE	LENGTH (L)	WIDTH (W)	HEIGHT (H)	STD. CTN. QTY.
G-1-S DBR	10 SOL - 2 STR	1/2-1	3/8 - 1	3/8-1	2.280	0.650	1.400	20

HD GROUND CLAMP WITH ADAPTER AND BRASS SCREWS



- Bronze clamps for copper water pipes with bronze adapters.
- Assembled with brass screws.

All dimensional data is listed in inches.

CAT. NO.	GROUND WIRE RANGE	PIPE SIZE	LENGTH (L)	WIDTH (W)	HEIGHT (H)	STD. CTN. QTY.
G-3 BS	8-4/0 STR	1/2-1	2.320	0.748	1.437	20



REBAR GROUND CLAMPS



Features

- Lay-in style clamp allows for continuous loop wiring.
- Cast silicon bronze connector & Stainless steel hardware.

Application

- For use with copper wire only.
- Harsh direct bury environments & Pool and Spa.
- Any commercial, industrial, maintenance application where ground wire needs to be connected to rebar.

Ratings

- cULus Listed UL467 Grounding & Bonding Equipment & Direct Bury.



*UL Listed for #4 STR - #2 STR.

All dimensional data is listed in inches.

CAT. NO.	FIG. NO.	GROUND WIRE RANGE	REBAR SIZE (IN)	LENGTH (L)	WIDTH (W)	HEIGHT (H)	STD. CTN. QTY.
RC38	1	8-6 SOL	0.375	1.14	0.74	0.75	25
RC50	2	8 SOL - 4 STR	0.500	1.35	0.83	0.91	25
RC58*	3	6 SOL - 2/0 STR	0.625	1.62	0.80	1.06	25