



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



G4X4LG6 SLTD Wiring Duct *Panduit Corporation*

Catalog Number	G4X4LG6
Manufacturer	Panduit Corporation
Description	The G4X4LG6 Panduct Lead-Free PVC Wide Slot Wiring Duct Feature A Wide Slot/Finger Design That Provides Greater Sidewall Rigidity and Is Suitable With A Range Of Wire Bundle Sizes. UL 94 Flame Class Of V-0 With A UL Recognized Continuous-Use Temperature Up to 122°F (50°C). Mounting Holes Provided. 4.0" X 4.0" (101.6 MM X 101.6 MM) and 6' (1.8 M) Long. Cover Sold Separately. Color Light Gray.
Weight per unit	0.0662 (lbs/each)
Product Category	Ducts, Raceways, Runways, Tray

Features

connection	Mounting Holes
Material	PVC
media	Yes

Material, Color, and Finish

Color	Light Gray
-------	------------

Dimensions and Weight

Length	NA
Size	4.25 x 4.10
Width	4.25

Descriptions

Description	SLTD WIRING DUCT
extra long description	PAN G4X4LG6 Panduct® G4X4LG6 Base W
Long Description	The G4X4LG6 Panduct Lead-Free PVC Wide Slot Wiring Duct feature a wide slot/finger design that provides greater sidewall rigidity and is suitable with a range of wire bundle sizes. UL 94 flame class of V-0 with a UL recognized continuous-use temperature up to 122°F (50°C). Mounting holes provided. 4.0" x 4.0" (101.6 mm x 101.6 mm) and 6' (1.8 m) long. Cover sold separately. Color Light Gray.
Product Type	Panduct® G4X4LG6 Base Wiring Duct



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	PANDUIT
GTIN	00074983545933
Manufacturers Part Number	G4X4LG6
UPC	074983545933

Taxonomies, Classifications, and Categories

Category Description	WIRE DUCT AND COVERS
Type	Base Wiring Duct

Packaging

Carton	60
Weight Per each	0.0662

Uses, Certifications, and Standards

Application	Wide slot/finger design provides greater sidewall rigidity and can be used in a wide range of applications
standard	RoHS Compliant, UL Recognized, CE Compliant; CSA Approved