



BURNDY Catalog Number
UPC Number
Description
Status

GAR2034
 7818102366599
 300-500CU 3IPS
 Active

Web Use
 BURNDY Product Line

Width (in)
 Length (in)
 Height (in)
 Size (Hex) or Size (Bolt)
 Size (Hex) or Size (Bolt) - in
 B Length (in)
 Width (Fraction)
 Height (Fraction) (in)

Dimensional

5.19
 2.38
 6.38
 1/2
 0.50
 3.75
 5-1/4
 6-3/8

Product Description

General

Mechanical Grounding Connector,
 Cable to Rod or Pipe, 300 - 500
 kcmil, 3" to 3-1/2" Rod, 3" Pipe,
 Bright Dipped

Type of U Bolt

Other

282

Approvals / Certifications

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards
 Rated for Direct Burial

Y
 Y
 Exempt
 N
 N
 UL467
 Y

Copper Tube Size (SCH40) - Range
 Rod Size (Range)
 Copper Solid Size (Range)
 Copper Stranded (Range)
 Rebar Size (Range)

Conductor(s)

3 IPS IPS
 3 in-3 1/2 in
 N/A
 300 kcmil-500 kcmil
 N/A

Type of Hardware
 Installation Torque
 Type of Plating
 Plated (Yes or No)
 Product Material

Physical

DURIUMâ€ Silicon Bronze
 480
 Bright Dipped
 N
 Copper Alloy

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175