

# Specifications



## Eaton GDB-2A

Eaton GDB Series Fast-acting fuse, 2A, 250 Vac or less, 32 Vdc (self certified)

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series GDB fast-acting fuse
<b>CATALOG NUMBER</b>	GDB-2A
<b>UPC</b>	051712431798
<b>PRODUCT HEIGHT</b>	20 mm
<b>PRODUCT DIAMETER</b>	5.2 mm
<b>PRODUCT WEIGHT</b>	0.7 g
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	CCC Marked CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	VDE
<b>GLOBAL CATALOG</b>	GDB-2A



Powering Business Worldwide

## Product specifications

AMPERAGE RATING	2 A
FREQUENCY RATING - MAX	50 Hz
FREQUENCY RATING - MIN	50 Hz
VOLTAGE DROP	150 mV maximum
INTERRUPT RATING	35 AIC at 250 Vac
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end
MATERIAL	Glass tube Nickel-plated brass end cap construction
QUANTITY	5
VOLTAGE RATING	250 Vac or less, 32 Vdc (self certified)
TYPE	Electronic
APPLICATION	Electronic circuits

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - GDB-2A](#)

[Eaton GDB fast-acting glass tube fuses data sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

