



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GDB3.15A 250V Fa Low-Break IEC Glass Fuse

*Bussmann Fuses*

Catalog Number	GDB3.15A
Manufacturer	Bussmann Fuses
Description	Eaton GDB Series Fast-Acting Fuse 3.15A, 250 Vac or Less, 32 VDC (Self Certified), GDB-3-15a
Weight per unit	0.0050 (lbs/each)
Product Category	Small Dimension Fuses

### Descriptions

Description	250V FA LOW-BREAK IEC GLASS FUSE
extra long description	BUSS GDB-3.15A BUSS SMALL DIMENSION
Features	Fast-acting, low breaking capacity 5 mm x 20 mm ferrule fuse designed to IEC 60127-2 for overcurrent protection of electronic circuits. Install into a Bussmann Series fuse holder, block, or fuse clip, or purchase with available axial leads for thru-hole installation Eaton's GDB fast-acting, low breaking capacity 5mm x 20mm ferrule fuses are designed to IEC 60127-2 for overcurrent protection of electronic circuits. Order in cartridge fuse format and install into a Bussmann Series fuse holder, block, or fuse
Long Description	Eaton GDB Series Fast-acting fuse 3.15A, 250 Vac or less, 32 Vdc (self certified), GDB-3-15A
Product Type	Buss Small Dimension Fuse

### Manufacturer Information

Brand	Eaton Bussmann series
GTIN	00051712431811
Manufacturers Part Number	GDB-3.15A
UPC	051712431811

### Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
----------------------	---------------------------

### Packaging

Carton	5
Weight Per each	0.005