



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GDB4A 4A 250V Fa Low-Break IEC Glass Fuse

Bussmann Fuses

Catalog Number	GDB4A
Manufacturer	Bussmann Fuses
Description	Eaton GDB Series Fast-Acting Fuse, 4A, 250 Vac or Less, 32 VDC (Self Certified)
Weight per unit	0.0020 (lbs/each)
Product Category	Small Dimension Fuses

Descriptions

Description	4A 250V FA LOW-BREAK IEC GLASS FUSE
extra long description	BUSS GDB-4A BUSS SMALL DIMENSION FU
Features	Fast-acting, low breaking capacity 5 mm x 20 mm ferrule fuse designed to IEC 60127-2 for overcurrent protection of electronic circuits. Install into a Bussmann Series fuse holder, block, or fuse clip, or purchase with available axial leads for thru-hole installation Eaton's GDB fast-acting, low breaking capacity 5mm x 20mm ferrule fuses are designed to IEC 60127-2 for overcurrent protection of electronic circuits. Order in cartridge fuse format and install into a Bussmann Series fuse holder, block, or fuse
Long Description	Eaton GDB Series Fast-acting fuse, 4A, 250 Vac or less, 32 Vdc (self certified)
Product Type	Buss Small Dimension Fuse

Manufacturer Information

Brand	Eaton
GTIN	00051712431828
Manufacturers Part Number	GDB-4A
UPC	051712431828

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
----------------------	---------------------------

Packaging

Carton	5
Weight Per each	0.002