



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GDB500MA 500MA 250V Fa Low-Break IEC Glass Fuse

Bussmann Fuses

Catalog Number	GDB500MA
Manufacturer	Bussmann Fuses
Description	Fuse, Fast Acting Fuse Speed, Ferrule End X Ferrule End Connection, 500 Ma, 250 V Ac, Glass (Tube);Brass (End Cap) Material, Ferrule Terminal, 5.2 MM Diameter, 20 MM Overall Length, 0.01 LB
Weight per unit	0.0100 (lbs/each)
Product Category	Small Dimension Fuses

Descriptions

Description	500MA 250V FA LOW-BREAK IEC GLASS FUSE
extra long description	BUSS GDB-500MA BUSS SMALL DIMENSION
Features	Fast-acting, low breaking capacity 5 mm x 20 mm ferrule fuse designed to IEC 60127-2 for overcurrent protection of electronic circuits. Install into a Bussmann Series fuse holder, block, or fuse clip, or purchase with available axial leads for thru-hole installation Eaton's GDB fast-acting, low breaking capacity 5mm x 20mm ferrule fuses are designed to IEC 60127-2 for overcurrent protection of electronic circuits. Order in cartridge fuse format and install into a Bussmann Series fuse holder, block, or fuse

Manufacturer Information

Brand	Eaton
GTIN	00051712431736
UPC	051712431736

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
----------------------	---------------------------

Packaging

Carton	5
Weight Per each	0.01