



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GE332MAXGN *Delisted* 74456 Eltrn BLST

Ge By Current Lamps

| | |
|------------------|-----------------------------------------------------------------------------------------------------------------------|
| Catalog Number | GE332MAXGN |
| Manufacturer | Ge By Current Lamps |
| Description | Ge Ultramax™, 60 HZ, Normal Ballast Factor, Instant Start, 9.5 In Length, 1.3 In Width, 1.18 In Height, 3 or 2- F32T8 |
| Weight per unit | 1.2 (lbs/each) |
| Product Category | Electronic Linear Fluorescent |

Features

| | |
|----------------|---------------|
| Ballast Factor | Normal |
| start type | Instant Start |

Dimensions and Weight

| | |
|--------|------|
| Height | 1.18 |
| Length | 9.5 |
| Width | 1.3 |

Descriptions

| | |
|------------------------|-----------------------------------------------------------------------------------------------------------------------|
| Description | *DELISTED* 74456 ELTRN BLST |
| extra long description | GEL GE332MAX-G-N 74456 ELECTRONIC B |
| Long Description | GE UltraMax™, 60 Hz, Normal Ballast Factor, Instant Start, 9.5 IN Length, 1.3 IN Width, 1.18 IN Height, 3 or 2- F32T8 |
| Product Type | 74456 Electronic Ballast |
| Special Features | GE332MAX-G-N (Replaces GE-332-MV-N) Designation |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | GE Current |
| GTIN | 00043168744560 |
| Manufacturers Part Number | GE332MAX-G-N |
| UPC | 043168744560 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------------|
| Category Description | ELECTRONIC BALLAST |
| Type | Ballasts_Fluorescent_Electronic |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 1.17 |

Uses, Certifications, and Standards

| | |
|------------------|----|
| Frequency Rating | 60 |
|------------------|----|