



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GK100N 1" Neo Gasket *Crouse-Hinds*

Catalog Number	GK100N
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Form 5 Gasket, Neoprene, Perforated Center, 1"
Weight per unit	0.0300 (lbs/each)
Product Category	Bodies & Covers

Features

dimensions	1.7800 IN X 0.0600 IN X 5.3800 IN
Form	Form 5

Material, Color, and Finish

Finish	Untreated
--------	-----------

Dimensions and Weight

Hub Size	1 in
----------	------

Descriptions

Description	1" NEO GASKET
extra long description	CRS-H GK100N 1 FORM 5 GASKET
Features	Form 5 malleable iron conduit bodies, covers and gaskets from Eaton's Crouse-Hinds Division are used in conduit systems to act as pull outlets for conductors being installed, provide openings for making splices and taps in conductors, make 90 degree bends in conduit runs, and provide access to conductors for maintenance and future system changes. Form 5 conduit bodies are manufactured in trade sizes 1/2" to 4", and are interchangeable with Appleton Form 35 conduit bodies. They are also available with a h
Long Description	Eaton Crouse-Hinds series Condulet Form 5 gasket, Neoprene, Perforated center, 1"
Product Type	1 Form 5 Gasket
Special Features	Perforated Center

Manufacturer Information

Brand	Eaton
GTIN	00782274756523
Manufacturers Part Number	GK100N
UPC	782274756523

Taxonomies, Classifications, and Categories

Category Description	HUB STYLE BOXES (GUAB, GUAT, ETC)
Type	Gasket



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	50
Weight Per each	0.03

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	UL 514B, CSA C22.2, CUL