



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)



## Fast-Acting Fuse

**GMA-1.5-R**

**UPC:**051712647816

**Dimensions:**

- **Height:** .788 IN
- **Length:** .25 IN
- **Width:** .197 IN

**Weight:**.005 LB

**Warranties:**

- Not Applicable

**Specifications:**

- **Type:** Electronic- small dimension
- **Application:** Electronic circuits
- **Amperage Rating:** 1.5A
- **Voltage Rating:** 250 Vac, 32 Vdc (self certified)
- **Interrupt Rating:** 10 kAIC at 125 Vac, 0.1 kAIC at 250 Vac
- **Fuse Indicator:** Non Indicating
- **Packaging Type:** Standard
- **Response Time:** 60 min maximum at 135%, 2 min maximum at 200%
- **Material:** Glass tube, nickel-plated brass endcaps
- **Connection:** Ferrule end X ferrule end

**Supporting documents:**

- [GMA 1.5A BUSS FUSE](#)

**Certifications:** No Data

**Product compliance:**

- RoHS Compliant
- CE Marked



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)



## Fast-Acting Fuse

**GMA-1.5-R**

**UPC:**051712647816

**Dimensions:**

- **Height:** .788 IN
- **Length:** .25 IN
- **Width:** .197 IN

**Weight:**.005 LB

**Warranties:**

- Not Applicable

**Specifications:**

- **Type:** Electronic- small dimension
- **Application:** Electronic circuits
- **Amperage Rating:** 1.5A
- **Voltage Rating:** 250 Vac, 32 Vdc (self certified)
- **Interrupt Rating:** 10 kAIC at 125 Vac, 0.1 kAIC at 250 Vac
- **Fuse Indicator:** Non Indicating
- **Packaging Type:** Standard
- **Response Time:** 60 min maximum at 135%, 2 min maximum at 200%
- **Material:** Glass tube, nickel-plated brass endcaps
- **Connection:** Ferrule end X ferrule end

**Supporting documents:**

- [GMA 1.5A BUSS FUSE](#)

**Certifications:** No Data

**Product compliance:**

- RoHS Compliant
- CE Marked