



Powering Business Worldwide

pe.eaton.com

Fast-Acting Fuse

BK/GMA-10-R

UPC:051712647205

Dimensions:

- **Height:** 1 IN
- **Length:** 2.3 IN
- **Width:** 2 IN

Weight:.002 LB

Warranties:

- Not Applicable

Specifications:

- **Type:** Electronic- small dimension
- **Application:** Electronic circuits
- **Amperage Rating:** 10A
- **Voltage Rating:** 125 Vac, 32 Vdc (self certified)
- **Interrupt Rating:** 150 AIC at 125 Vac
- **Fuse Indicator:** Non Indicating
- **Packaging Type:** Standard
- **Used With:** out axial leads
- **Response Time:** 60 min maximum at 135%, 2 min maximum at 200%
- **Material:** Glass tube, nickel-plated brass endcaps
- **Connection:** Ferrule end X ferrule end
- **Quantity:** Bulk 100

Supporting documents:

- [GMA 10A BUSS FA BK 100 BOX -R](#)

Certifications: No Data

Product compliance:

- CE Marked
- RoHS Compliant



