

Specifications



Eaton GMA-15-R

Eaton GMA Series Fast-acting fuse, 15A, 125 Vac, 32 Vdc

General specifications

PRODUCT NAME	Eaton Bussmann series GMA Fast-acting glass tube fuse
CATALOG NUMBER	GMA-15-R
UPC	051712647878
EAN	5027590157605
PRODUCT HEIGHT	20 mm
PRODUCT DIAMETER	5 mm
PRODUCT WEIGHT	0.678 g
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant

Product specifications

AMPERAGE RATING	15 A
INTERRUPT RATING	150 AIC at 125 Vac
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end
RESPONSE TIME	60 min at 135%, 2 min at 200%
MATERIAL	Glass tube Nickel-plated brass end cap construction
QUANTITY	5
VOLTAGE RATING	125 Vac, 32 Vdc
TYPE	Electronic
APPLICATION	Electronic circuits

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton GMA time delay
glass tube fuses data
sheet](#)

[Eaton Specification Sheet -
GMA-15-R](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

