


# GT500RW

Gotcha Sensor with two weatherproof, corrosionproof floodlights, molded gaskets and corrosionproof universal cover plate. Lamps not supplied.

Color: White

Weight: 1.6 lbs



## Technical Specifications

### UL Listing:

Suitable for wet locations.

### Voltage:

120 volts AC 60 Hz.

### Power Consumption:

1 watt.

### Time Adjustment:

10 seconds to 5 minutes.

### Surge Protection:

Withstands up to 6000 volts.

### Photoelectric Control:

Deactivates lights during daylight.

### Detector Sensitivity:

Adjustable from 100% to 50%.

### Wall Switch Manual Override:

Two flip logic prevents activation by momentary power outages. Override resets to auto after 6 hours or at dawn. No extra wiring needed.

### Sensor Housing:

Made of tough, corrosion resistant polycarbonate.

### Floodlights:

Made of tough, corrosion-resistant polycarbonate. For extra or replacement floodlights, order cat# TUFFY in your choice of color. Accepts PAR-38 lamps, medium base, 150 watts max. Lamps not included.

### Detection:

110° view.

### Patents:


RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.

# GT500RW

Gotcha Sensor with two weatherproof, corrosionproof floodlights, molded gaskets and corrosionproof universal cover plate. Lamps not supplied.

Color: White

Weight: 1.6 lbs



## Technical Specifications

### UL Listing:

Suitable for wet locations.

### Voltage:

120 volts AC 60 Hz.

### Power Consumption:

1 watt.

### Time Adjustment:

10 seconds to 5 minutes.

### Surge Protection:

Withstands up to 6000 volts.

### Photoelectric Control:

Deactivates lights during daylight.

### Detector Sensitivity:

Adjustable from 100% to 50%.

### Wall Switch Manual Override:

Two flip logic prevents activation by momentary power outages. Override resets to auto after 6 hours or at dawn. No extra wiring needed.

### Sensor Housing:

Made of tough, corrosion resistant polycarbonate.

### Floodlights:

Made of tough, corrosion-resistant polycarbonate. For extra or replacement floodlights, order cat# TUFFY in your choice of color. Accepts PAR-38 lamps, medium base, 150 watts max. Lamps not included.

### Detection:

110° view.

### Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.