



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GUAL14 1/2" Gual Body&CVR

*Crouse-Hinds*

Catalog Number	GUAL14
Manufacturer	Crouse-Hinds
Description	Conduit Outlet Box With Cover, Electrogalvanized and Aluminum Acrylic Paint (Body);Natural (Cover), L Body Type, 1/2 In Trade Size, Threaded Connection, Round, 3 In (Cover) Opening Size, 2 Hubs, 1/2 In Hub Size, (2) Side Hub Location, L Configuration, 2-1/2 In Width, 1-13/16 In Height, (4) Pad, 1.65 LB/Ea
Weight per unit	1.7 (lbs/each)
Product Category	Bodies & Covers

### Features

Cable Entry dimensions	(2) Side 3.3800 IN X 2.2500 IN X 3.3800 IN
------------------------	---

### Dimensions and Weight

Size	1/2 in
------	--------

### Descriptions

Construction	Explosionproof, Dust-Ignitionproof, Raintight
Description	1/2" GUAL BODY&CVR
extra long description	CRS-H GUAL14 1/2 OUTLET BX 2 CVR FO
Features	Crouse-Hinds series GUA and GUR explosionproof conduit outlet boxes are installed in conduit systems in hazardous areas to protect conductors in threaded rigid conduit, act as pull and splice boxes, change conduit direction, and provide access to conductors for maintenance and future system changes. GUA and GUR outlet boxes are certified for Class I, Division 1, Groups B, C, D and Class II, Division 1, Groups E, F, G. GUA boxes are available in ten different hub arrangements, maximizing flexibility in th

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274464701
UPC	782274464701

### Taxonomies, Classifications, and Categories

Category Description	HUB STYLE BOXES (GUAB, GUAT, ETC)
Type	Conduit outlet box with cover

### Packaging

Carton	1
Package	2
Weight Per each	1.65



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

standard

UL 886, CSA C22.2

---