



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL2325SW LKG WT S/SHRD FLG-Inlt, 20A 250V, L6-20P

Hubbell Wiring Devices

Catalog Number	HBL2325SW
Manufacturer	Hubbell Wiring Devices
Description	Watertight Safety-Shroud®, Locking Devices, Twist-Lock®, Flanged Inlet, 20A 250V Ac, 2-Pole 3-Wire Grounding, Nema L6-20P, Screw Terminal, Gray.
Weight per unit	0.6000 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	20
connection	Screw Terminals
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
insulation	Insulated Body
Number of Wires	3-Wire
Phase	1
Poles	2-Pole
Voltage Rating	250 V
Wattage	5,000
Wire Size	#16 to #8

Dimensions and Weight

Size	3.75 in x 3.75 in x 2.28 in
------	-----------------------------

Descriptions

Description	LKG WT S/SHRD FLG-INLT, 20A 250V, L6-20P
extra long description	HWDK HBL2325SW LKG WT S/SHRD FLG-IN
Long Description	Watertight Safety-Shroud®, Locking Devices, Twist-Lock®, Flanged Inlet, 20A 250V AC, 2-Pole 3-Wire Grounding, NEMA L6-20P, Screw Terminal, Gray.
Product Type	LKG WT S/SHRD FLG-Inlt, 20A 250V, L6-20P
Special Features	Standard Product

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585231143
Manufacturers Part Number	HBL2325SW
UPC	783585231143

Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Flanged Inlet



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	5
Weight Per each	0.6

Uses, Certifications, and Standards

Application	Extra Heavy Duty Industrial
environmental conditions	Watertight
Mounting	Screw Mount
nema rating	L6-20P
standard	UL Listed, CSA Certified To Type 4, 4X And Type 12