



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL2333 LKG Conn, 20A 277V Ac, L7-20R, B/W Hubbell Wiring Devices

Catalog Number	HBL2333
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Twist-Lock®, Industrial, Female Insulgrip® Connector Body, 20A 277V Ac, 2-Pole 3-Wire Grounding, Nema L7-20R, Screw Terminal, Black and White Nylon.
Weight per unit	0.3500 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

connection	Pressure Screw Terminal
Current Rating	20
insulation	Insulated Body
Material	Nylon
Number of Conductors	3
pallet quantity	2880
Poles	2-Pole
Voltage Rating	277

Dimensions and Weight

Size	2.26 in x 2.26 in x 3.86 in
------	-----------------------------

Descriptions

Description	LKG CONN, 20A 277V AC, L7-20R, B/W
extra long description	HWDK HBL2333 LKG CONN, 20A 277V AC,
Long Description	Locking Devices, Twist-Lock®, Industrial, Female Insulgrip® Connector Body, 20A 277V AC, 2-Pole 3-Wire Grounding, NEMA L7-20R, Screw Terminal, Black and White Nylon.
Product Type	LKG Conn, 20A 277V Ac, L7-20R, B/W
Special Features	Standard Product

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585037929
Manufacturers Part Number	HBL2333
UPC	783585037929

Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Connector Body



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	30
Weight Per each	0.35

Uses, Certifications, and Standards

Mounting	Cord
nema rating	L7-20R
standard	Certified to CSA C22.2 No.42;Fed.Spec. W-C-596;Listed to UL 498