



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HBL2730SW LKG WT S/SHRD RCPT, 30A3P 480V, L16-30R

Hubbell Wiring Devices

Catalog Number	HBL2730SW
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Twist-Lock®, Watertight Safety-Shroud®, Receptacle, 30A 3-Phase Delta 480V Ac, 3-Pole 4-Wire Grounding, Nema L16-30R, Screw Terminal, PBT Housing and Flange, Gray
Weight per unit	0.3080 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	30
connection	Screw Terminal
Current Rating	30
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	4-Wire
pallet quantity	1000
Phase	3
Poles	3-Pole
Voltage Rating	480 V
Wattage	14,400
Wire Size	#16 to #8

### Dimensions and Weight

Size	3.75 in x 3.75 in x 2.9 in
------	----------------------------

### Descriptions

Description	LKG WT S/SHRD RCPT, 30A3P 480V, L16-30R
extra long description	HWDK HBL2730SW LKG WT S/SHRD RCPT,
Long Description	Locking Devices, Twist-Lock®, Watertight Safety-Shroud®, Receptacle, 30A 3-Phase Delta 480V AC, 3-Pole 4-Wire Grounding, NEMA L16-30R, Screw Terminal, PBT housing and flange, Gray
Product Type	LKG WT S/SHRD RCPT, 30A3P 480V, L16-30R
Special Features	Shrouded Watertight Construction

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585231907
Manufacturers Part Number	HBL2730SW
UPC	783585231907



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	RECEPTACLE

## Packaging

Carton	1
Package	5
Weight Per each	0.308

## Uses, Certifications, and Standards

Application	Heavy Duty Industrial Shrouded Watertight
environmental conditions	Watertight
Mounting	Screw Mount
nema rating	L16-30R
standard	UL Listed, CSA Certified To Type 4, 4X And Type 12