



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL8450A SGL RCPT, 3P4W, 50A 3PH 250V, 15-50R, BK *Hubbell Wiring Devices*

Catalog Number	HBL8450A
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacles, Flush Receptacle, Industrial Grade, 3-Pole 4-Wire Grounding, 50A 3 Phase 250V Ac, 15-50R, Black, Single Pack.
Weight per unit	0.6500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	50
connection	Back and Side Wired Screw Terminals
Current Rating	50
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	4-Wire
pallet quantity	1800
Phase	3
Poles	3-Pole
Voltage Rating	250 VAC
Wattage	12500
Wire Size	#12 to #6

Dimensions and Weight

Size	Standard Sized Product
------	------------------------

Descriptions

Description	SGL RCPT, 3P4W, 50A 3PH 250V,15-50R,BK
extra long description	HWDK HBL8450A SGL RCPT, 3P4W, 50A 3
Long Description	Straight Blade Devices, Receptacles, Flush Receptacle, Industrial Grade, 3-Pole 4-Wire Grounding, 50A 3 Phase 250V AC, 15-50R, Black, Single Pack.
Product Type	SGL RCPT, 3P4W, 50A 3PH 250V, 15-50R, BK
Special Features	Standard

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585015156
Manufacturers Part Number	HBL8450A
UPC	783585015156

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	SINGLE RECEPTACLE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	5
Weight Per each	0.65

Uses, Certifications, and Standards

Application	Heavy Duty
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	15-50R
standard	CSA Certified;NEMA® WD-6 Compliant;UL Listed File E2186