

Twist-Lock® Devices Mechanical Interlock Replacement Part Replacement Switch

HUBBELL

Ordering Information

Description	Product Type	UPC	Catalog Number
Replacement switch	CircuitLock Accessory	783585955179	HBLDS3RS

Listings

Listed to UL Standard
CSA Certified TYPE 4, 4X and TYPE 12K Enclosure Rating



Accessories

Enclosure Accommodation Switched Safety Enclosures, 30A HBLDS S
Disconnects & HBLMITL

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current voltage

Dielectric Voltage Withstands 3,000V Min
Max. Working Voltage 600V RMS
Operations Mechanical 10,000 cycles; Electrical 6,000 cycles

Mechanical

Impact Resistance In accordance with UL 746C
Mounting External full adjustable feet
Product Identification Identification and ratings are part of the external label and
receptacle face
Terminal Identification In accordance with UL, CSA

Environmental

Flammability Meets UL 94V0 material classification
Moisture Resistance IP66 suitability
Operating Temperature Maximum continuous +75°C; Minimum continuous -40°C
UV Resistance All exposed materials are UV stabilized

Resources

[eCatalog](#)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

