



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HFD2125 Type HFD 2 Pole 125A Trip 600V Class 65KA At 480V

Eaton Corp

Catalog Number	HFD2125
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, F-Frame, HFD, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Two-Pole, 125 A, 600 Vac, 250 VDC, 100 Kaic At 240 Vac, 65 Kaic At 480 Vac, Load Side, 50/60 HZ
Weight per unit	2.9 (lbs/each)
Product Category	2 Pole

Features

Current Rating	125 A
dimensions	7.5000 IN X 5.0000 IN X 3.2500 IN
media	Yes
Poles	2
Trip Type	Fixed thermal, fixed magnetic
Voltage Rating	600 VAC, 250 VDC

Descriptions

Description	TYPE HFD 2 POLE 125A TRIP 600V CLASS 65KA AT 480V
extra long description	ETN HFD2125 HFD 2P 125A TRIP 600V C
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, F-frame, HFD, Complete breaker, Fixed thermal, Fixed magnetic trip type, Two-pole, 125 A, 600 Vac, 250 Vdc, 100 kAIC at 240 Vac, 65 kAIC at 480 Vac, Load side, 50/60 Hz
Product Type	HFD 2P 125A Trip 600V CL 65KA 480V No

Manufacturer Information

Brand	Eaton
GTIN	00786679175477
Manufacturers Part Number	HFD2125
UPC	786679175477

Taxonomies, Classifications, and Categories

Type	Molded case circuit breaker
------	-----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	2.93

Uses, Certifications, and Standards

Application	Other
Frequency Rating	50/60 Hz
standard	UL Listed