



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HFD3200 HFD 3P 600VAC Rated Load Terms Only

Eaton Corp

Catalog Number	HFD3200
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, F-Frame, HFD, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Three-Pole, 200 A, 600 Vac, 250 VDC, Load Side, 50/60 HZ
Weight per unit	4.5 (lbs/each)
Product Category	3 Pole

Features

Current Rating	200 A
dimensions	3.3800 IN X 4.1300 IN X 4.1300 IN
media	Yes
Poles	3
Trip Type	Fixed thermal, fixed magnetic
Voltage Rating	600 VAC, 250 VDC

Descriptions

Description	HFD 3P 600VAC RATED LOAD TERMS ONLY
extra long description	ETN HFD3200 HFD 3P 600VAC RATED LOA
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, F-frame, HFD, Complete breaker, Fixed thermal, Fixed magnetic trip type, Three-pole, 200 A, 600 Vac, 250 Vdc, Load side, 50/60 Hz
Product Type	HFD 3P 600VAC Rated Load Terms Only

Manufacturer Information

Brand	Eaton
GTIN	00786679015438
Manufacturers Part Number	HFD3200
UPC	786679015438

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	4.5

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Frequency Rating	50 to 60 Hz
standard	UL Listed