



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HLBC4LS9FSD2WE01 4" Led Slim DWNLCT CCT Canless or Retrofit 120/277V *Cooper Lighting Solutions*

Catalog Number	HLBC4LS9FSD2WE01
Manufacturer	Cooper Lighting Solutions
Description	4" Downlight, 600/900 Selectable Lumens 90 Cri Selectable CCT D2W Option 120/277V 60HZ, 0-10V Dimmable, Matte White Flange Canless or Retrofit Installation Compliant All States But Ca
Weight per unit	1.7 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.04
Lamp Type	LED
Voltage Rating	120/277V
Wattage	13

Material, Color, and Finish

Finish	Matte
Style	(blank)

Descriptions

Description	4" LED SLIM DWNLCT CCT CANLESS OR RETROFIT 120/277V
extra long description	CLS HLBC4LS9FSD2WE010MWR 4" HLB COM
Long Description	4" downlight, 600/900 selectable lumens 90 CRI selectable CCT D2W option 120/277V 60Hz, 0-10V dimmable, matte white flange canless or retrofit installation compliant all states but CA
Product Type	4" HLB Comfort, LS, 5CCT, D2W, R, Unv
Special Features	Available in 4" and 6"

Manufacturer Information

Brand	Cooper Lighting Solutions
GTIN	00080083263233
Manufacturers Part Number	HLBC4LS9FSD2WE010MWR
UPC	080083263233

Taxonomies, Classifications, and Categories

Category Description	LED GENERAL PURPOSE LIGHTING
Type	HLBC Slim Regressed Canless Downlight

Packaging

Carton	1
Weight Per each	1.65



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	lighting
Mounting	CEILING
standard	Energy Star Certified; IECC Compliant; RoHS Compliant; Title 20 Compliant; Title 24 Compliant; UL Listed