

Eaton HP404040SH

Catalog Number: HP404040SH

Eaton house panel, 400A, Aluminum, No bypass, NEMA 3R, Underground, 22 kAIC, Lug landings for compression, lugs not included, CSR2200, Surface mounting, C:40, S:1, SP:40, BRH/BWH, Ring, Type BR breakers, 120/240V, 4306, Single-phase



General specifications

Product Name	Catalog Number
Eaton house panel	HP404040SH
UPC	Product Length/Depth
782114868713	6 in
Product Height	Product Width
44 in	29.75 in
Product Weight	Warranty
155 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
EUSERC Approved	UL Listed

defaultTaxonomyAttributeLabel

Type

House panel

Interrupt rating

10 kAIC

Enclosure

NEMA 3R

Secondary circuit breaker

BRH/BWH

Amperage Rating

400 A

Line

Lug landings for compression, lugs not included

Mounting

Surface

Number of spaces

40

Security

Ring

Voltage rating

120/240 V

Number of sockets

1

Used with

Type BR breakers

Bypass

None

Number of circuits

40

Bus material

Aluminum

Feed type

Bottom

Main circuit breaker

CSR2200

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - METER BREAKER HP40SH and SHA, HP404040SH and SHA

Specifications and datasheets

Technical Data Residential Meter Breakers: Type CH and BR Residential
Eaton Specification Sheet - HP404040SH



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)