



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HR175DX39 175W ED28 Mercury Vapor White Mogul Base Lamp

Ge By Current Lamps

| | |
|------------------|--|
| Catalog Number | HR175DX39 |
| Manufacturer | Ge By Current Lamps |
| Description | Hid Mercury Vapor Lamp, 50, 3900 K, 7800 LM Brightness (Lumens), 175 W, 318 V, White, Hard Glass Material, 20000 H Average Life, Mogul Screw Base, H39 Ansi Ballast Code, Non Dimmable, 3.5 In Diameter, 8.25 In Length, 30.3 % Mercury Content, 0.53 LB |
| Weight per unit | 0.5300 (lbs/each) |
| Product Category | Hid Mercury Vapor Lamps |

Features

| | |
|---------|------|
| Base | E39 |
| lumens | 7800 |
| Wattage | 175 |

Material, Color, and Finish

| | |
|-----------------------------|---------------------------|
| Color | Delux white |
| color rendering index (cri) | 50.0 |
| Style | Open or enclosed fixtures |

Descriptions

| | |
|------------------------|---|
| Description | 175W ED28 MERCURY VAPOR WHITE MOGUL BASE LAMP |
| extra long description | GEL HR175DX39 24062 MERCURY |
| Special Features | 8.25IN Length |

Manufacturer Information

| | |
|-------|----------------------|
| Brand | Ge Traditional Lamps |
| GTIN | 00043168240628 |
| UPC | 043168240628 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------|
| Category Description | MERCURY VAPOR |
|----------------------|---------------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 12 |
| Weight Per each | 0.53 |

Uses, Certifications, and Standards

| | |
|-------------|----------------------------|
| Application | Universal burning position |
|-------------|----------------------------|