



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HS14 7/32" High Speed Steel Drill

L.H. Dottie CO.

Catalog Number	HS14
Manufacturer	L.H. Dottie CO.
Description	High Speed Drill, M2 Grade, Steel Material, Black/Gold Finish, Split Point Type, 135 Deg Split Drill Point, 7/32 In. Fractional Size, 3-3/4 In. Overall Length, 3/16 In. Shank Diameter
Weight per unit	0.0170 (lbs/each)
Product Category	Bits, Parts, Accessories

### Features

Grade	M2
Material	High Speed Steel
Number of Pieces	2
Point Type	Split Point
Shank Diameter	3/16

### Material, Color, and Finish

Finish	Black/Gold
--------	------------

### Dimensions and Weight

Overall Length	3-3/4
----------------	-------

### Descriptions

Description	7/32" HIGH SPEED STEEL DRILL
extra long description	DOTTIE HS14 7/32" High Speed Steel
Long Description	High Speed Drill, M2 grade, Steel material, Black/Gold finish, Split Point Type, 135 DEG Split drill point, 7/32 in. fractional size, 3-3/4 in. overall length, 3/16 in. shank diameter
Product Type	7/32" High Speed Steel Drills
Special Features	Features: Industrial Quality, Heavy Duty Jobber Length, Fractional Sizes

### Manufacturer Information

Brand	L.H. Dottie CO.
GTIN	00781002293149
Manufacturers Part Number	HS14
UPC	781002293149

### Taxonomies, Classifications, and Categories

Category Description	TOOL BAG/POUCHES
Type	High Speed Drill

### Packaging

Carton	12
Weight Per each	0.017



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Application ..... For Steel, Steel Forging, Cast Iron and Other Work Materials .....