

# Specifications

## Eaton I52

Eaton strain relief I-Grip,  
0.52-0.73" cord diameter,  
7.00" mesh length,  
Galvanized Steel

### Product specifications

<b>TYPE</b>	Strain relief I-Grip
<b>CORD DIAMETER</b>	0.52-0.73 in
<b>MATERIAL</b>	Galvanized Steel
<b>MESH LENGTH</b>	7.00 in

### General specifications

<b>PRODUCT NAME</b>	Eaton strain relief I-Grip
<b>CATALOG NUMBER</b>	I52
<b>UPC</b>	040893650906
<b>PRODUCT LENGTH/DEPTH</b>	8 in
<b>PRODUCT HEIGHT</b>	0.5 in
<b>PRODUCT WIDTH</b>	2.5 in
<b>PRODUCT WEIGHT</b>	0.04 lb
<b>CERTIFICATIONS</b>	CSA Certified



*Powering Business Worldwide*

# Specifications

## Eaton I52

Eaton strain relief I-Grip,  
0.52-0.73" cord diameter,  
7.00" mesh length,  
Galvanized Steel

### Product specifications

<b>TYPE</b>	Strain relief I-Grip
<b>CORD DIAMETER</b>	0.52-0.73 in
<b>MATERIAL</b>	Galvanized Steel
<b>MESH LENGTH</b>	7.00 in

### General specifications

<b>PRODUCT NAME</b>	Eaton strain relief I-Grip
<b>CATALOG NUMBER</b>	I52
<b>UPC</b>	040893650906
<b>PRODUCT LENGTH/DEPTH</b>	8 in
<b>PRODUCT HEIGHT</b>	0.5 in
<b>PRODUCT WIDTH</b>	2.5 in
<b>PRODUCT WEIGHT</b>	0.04 lb
<b>CERTIFICATIONS</b>	CSA Certified



*Powering Business Worldwide*