

Specifications

Eaton I70

Eaton strain relief I-Grip,
0.70-0.85" cord diameter,
8.50" mesh length,
Galvanized Steel

Product specifications

TYPE	Strain relief I-Grip
CORD DIAMETER	0.70-0.85 in
MATERIAL	Galvanized Steel
MESH LENGTH	8.50 in

General specifications

PRODUCT NAME	Eaton strain relief I-Grip
CATALOG NUMBER	I70
UPC	040893650913
PRODUCT LENGTH/DEPTH	10.5 in
PRODUCT HEIGHT	0.75 in
PRODUCT WIDTH	2.5 in
PRODUCT WEIGHT	0.055 lb
CERTIFICATIONS	CSA Certified



Powering Business Worldwide

Specifications

Eaton I70

Eaton strain relief I-Grip,
0.70-0.85" cord diameter,
8.50" mesh length,
Galvanized Steel

Product specifications

TYPE	Strain relief I-Grip
CORD DIAMETER	0.70-0.85 in
MATERIAL	Galvanized Steel
MESH LENGTH	8.50 in

General specifications

PRODUCT NAME	Eaton strain relief I-Grip
CATALOG NUMBER	I70
UPC	040893650913
PRODUCT LENGTH/DEPTH	10.5 in
PRODUCT HEIGHT	0.75 in
PRODUCT WIDTH	2.5 in
PRODUCT WEIGHT	0.055 lb
CERTIFICATIONS	CSA Certified



Powering Business Worldwide