



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## IC1P 4IN Ic HSG

*Lithonia Lighting - Acuity*

Catalog Number	IC1P
Manufacturer	Lithonia Lighting - Acuity
Description	The Energy-Efficient, Air-Loc Sealed Double Wall Construction Housing Stops Infiltration and Exfiltration Of Air, Reducing Heating and Cooling Costs Without An Extra Gasket. The 4-Inch Ic Housing Is Optimized For PAR20 Gimbal and Higher Wattage 120-Volt MR16 Lamps and Can Be Completely Covered With Insulation.
Weight per unit	3.5 (lbs/each)
Product Category	Incandescent Recessed Architec

### Features

Lamp Type	Incandescent
Material	Aluminum
Maximum Operating Temperature	25
Number of Lamps	1
Shape	Round

### Dimensions and Weight

Height	8
Length	15
Width	15

### Descriptions

Construction	New Construction
Description	4IN IC HSG
extra long description	LITH IC1P 4IN Incandescent New Cons
Long Description	The energy-efficient, Air-Loc sealed double wall construction housing stops infiltration and exfiltration of air, reducing heating and cooling costs without an extra gasket. The 4-inch IC housing is optimized for PAR20 gimbal and higher wattage 120-volt MR16 lamps and can be completely covered with insulation.
Product Type	Housing

### Manufacturer Information

Brand	JUNO
GTIN	00661209077196
Manufacturers Part Number	IC1P
UPC	661209077196

### Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
----------------------	---------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Trade Size

aperture size ..... 4 in

## Packaging

Carton ..... 1

Package ..... 4

Weight ..... 5

Weight Per each ..... 3.5

## Uses, Certifications, and Standards

Application ..... Residential

environmental conditions ..... Indoor

Mounting ..... Recessed

standard ..... UL