



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## IC22R 6" Ic Rated Remodel Reces

*Lithonia Lighting - Acuity*

Catalog Number	IC22R
Manufacturer	Lithonia Lighting - Acuity
Description	These Ic-Rated 6-Inch Incandescent Housings Feature An Air-Loc Seal to Stop Infiltration and Exfiltration Of Air, Reducing Heating and Cooling Costs.
Weight per unit	2.0 (lbs/each)
Product Category	Incandescent Recessed Architec

### Features

Lamp Type	Incandescent
Maximum Operating Temperature	25
Number of Lamps	1
Shape	Round

### Dimensions and Weight

Height	7.125
Length	13.75
Width	7.125

### Descriptions

Construction	Remodel
extra long description	LITH IC22R 6IN Incandescent Remodel
Features	Contractor Select
Long Description	These IC-rated 6-inch incandescent housings feature an Air-Loc seal to stop infiltration and exfiltration of air, reducing heating and cooling costs.
Product Type	Housing

### Manufacturer Information

Brand	JUNO
GTIN	00661209017673
Manufacturers Part Number	IC22R
UPC	661209017673

### Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
Type	Housing

### Trade Size

aperture size	6 in
---------------	------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	6
Weight	2
Weight Per each	1.96

## Uses, Certifications, and Standards

Application	Residential
environmental conditions	Indoor
Mounting	Recessed
standard	cUL,UL