



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IC926 6" Slope Ic Rated Recess

Lithonia Lighting - Acuity

Catalog Number	IC926
Manufacturer	Lithonia Lighting - Acuity
Description	The Double Wall New Construction Housing For Use In 2/12 to 6/12 Pitch Slopes, 9 to 27 Degrees, Can Be Completely Covered With Insulation.
Weight per unit	4.0 (lbs/each)
Product Category	Incandescent Recessed Architec

Features

Hardware	Yes
Lamp Type	Incandescent
Material	Aluminum
Maximum Operating Temperature	25
Number of Lamps	1
Power Source	Hardwired
Shape	OVAL
Voltage Rating	120
Warranty	1

Material, Color, and Finish

Color	Unfinished
-------	------------

Dimensions and Weight

Height	7.625
Length	16.3125
Width	13.5

Descriptions

Construction	New Construction
Description	6" SLOPE IC RATED RECESS
extra long description	LITH IC926 6IN Incandescent Slope C
Long Description	The double wall new construction housing for use in 2/12 to 6/12 pitch slopes, 9 to 27 degrees, can be completely covered with insulation.
Product Type	Housing



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	JUNO
GTIN	00661209000897
Manufacturers Part Number	IC926
UPC	661209000897

Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
----------------------	---------------------------

Trade Size

aperture size	6 in
---------------	------

Packaging

Carton	1
Package	4
Weight	4
Weight Per each	3.97

Uses, Certifications, and Standards

Application	Education,Government,Healthcare,Hospitality,House of Worship,Offices & Banks,Residential,Retail
environmental conditions	Indoor
Mounting	Recessed
standard	CSA,UL